




AC-1A-MD-3/8				AC-1A-MD-1/2			
Item	Part Number	QTY REQ	Description	Item	Part Number	QTY REQ	Description
1	0115-0062-1000	4	#7-19 x 1-7/16" Long Self-Tapping Screw (Stainless)	1	0115-0062-1000	4	#7-19 x 1-7/16" Long Self-Tapping Screw (Stainless)
2	0115-0075-1000	1	Cover with 3/8" OD Inlet (Polypropylene)	2	0115-0060-1000	1	Cover with 1/2" OD Inlet (Polypropylene)
5	0115-0018-1000	1	1/16" CS x 1-7/16" OD "O" Ring for Cover (Buna N)	5	0115-0018-1000	1	1/16" CS x 1-7/16" OD "O" Ring for Cover (Buna N)
6	0115-0119-1000	1	Encapsulated Impeller (Polypropylene)	6	0115-0119-1000	1	Encapsulated Impeller (Polypropylene)
7	0115-0032-1000	1	Shaft (316 Stainless Steel)	7	0115-0032-1000	1	Shaft (316 Stainless Steel)
8	0115-0033-1000	1	Thrust Washer (Carbon/Teflon)	8	0115-0033-1000	1	Thrust Washer (Carbon/Teflon)
11	0115-0074-1000		Rear Housing with 3/8" OD Outlet (Polypropylene)	10	0115-0059-1000	1	Rear Housing with 1/2" OD Outlet(Polypropylene)
12	Not Available		Motor Assembly (115V 50/60 Hz) or (230V 50/60 Hz)	12	Not Available		Motor Assembly (115V 50/60 Hz) or (230V 50/60 Hz)
AC-1C-MD				Materials in contact with the solution: Polypropylene, Buna N, 316 Stainless Steel, Carbon/Teflon Washer.			
1	0115-0062-1000	4	#7-19 x 1-7/16" Long Self-Tapping Screw (Stainless)	Note: Contact Factory for other materials and/or parts not listed. Special voltage motors are available upon special order.			
2	0115-0058-1000	1	Cover with 1/4" MPT Inlet (Polypropylene)				
5	0115-0018-1000	1	1/16" CS x 1-7/16" OD "O" Ring for Cover (Buna N)				
6	0115-0119-1000	1	Encapsulated Impeller (Polypropylene)				
7	0115-0032-1000	1	Shaft (316 Stainless Steel)				
8	0115-0033-1000	1	Thrust Washer (Carbon/Teflon)				
9	0115-0057-1000	1	Rear Housing with 1/4" MPT Outlet (Polypropylene)				
12	Not Available		Motor Assembly (115V 50/60 Hz) or (230V 50/60 Hz)				
WARRANTY: https://www.marchpump.com/distributors/							
For the General Installation Manual, see this link https://www.marchpump.com/wp-content/uploads/2019/07/march-pump-general-installation-guide-0750-040.pdf							
Or Scan QR Code							
							
				0115-0035-1100-Rev 8/28/2025			